

Siemens Healthcare Diagnostics, the leading clinical diagnostics company, is committed to providing clinicians with the vital information they need for the accurate diagnosis, treatment and monitoring of patients. Our comprehensive portfolio of performance-driven systems, unmatched menu offering and IT solutions, in conjunction with highly responsive service, is designed to streamline workflow, enhance operational efficiency and support improved patient care.

Trademarks and brands are the property of their respective owners.

Product availability may vary from country to country and is subject to varying regulatory requirements. Please contact your local representative for availability.

#### Global Siemens Headquarters

Siemens AG  
Wittelsbacherplatz 2  
80333 Muenchen  
Germany

#### Global Siemens Healthcare Headquarters

Siemens AG  
Healthcare Sector  
Henkestrasse 127  
91052 Erlangen  
Germany  
Telephone: +49 9131 84 - 0  
[www.siemens.com/healthcare](http://www.siemens.com/healthcare)

#### Global Division

Siemens Healthcare Diagnostics Inc.  
511 Benedict Avenue  
Tarrytown, NY 10591-5005  
USA  
[www.usa.siemens.com/diagnostics](http://www.usa.siemens.com/diagnostics)

[www.usa.siemens.com/diagnostics](http://www.usa.siemens.com/diagnostics)

## MicroScan<sup>®</sup> Dried Conventional Gram Positive Panels

December 2010

Answers for life.

**SIEMENS**

# Dried Conventional Gram Positive Panels

Abbr.	Antimicrobial Agents	B1017-200 Pos Combo 20	B1017-201 Pos Combo 21	B1017-209 Pos Combo 29	B1017-211 Pos Combo 33	B1017-214 Pos Combo 34	B1017-202 Pos BP Combo 20	B1017-206 Pos BP Combo 23	B1017-210 Pos MIC 26	B1017-212 Pos MIC 29	B1027-201 MICroSTREP plus	Abbr.
Aug	Amoxicillin/K Clavulanate	4/2	4/2	4/2	4/2	4/2	4/2	4/2	4/2	4/2	0.5/0.25-4/2	Aug
Am	Ampicillin	0.25-0.5, 2-8	0.25-0.5, 2-8	2-8	2-8	2-8	0.25, 2-8	0.25, 2-8	2-8	2-8	0.06-4	Am
A/S	Ampicillin/Sulbactam	–	8/4-16/8	8/4-16/8	8/4-16/8	8/4-16/8	8/4-16/8	8/4-16/8	8/4-16/8	8/4-16/8	–	A/S
Azi	Azithromycin	–	–	–	–	–	2-4	–	–	–	0.25-2	Azi
Cfr	Cefaclor	–	–	–	–	–	–	–	–	–	0.5-4	Cfr
Cfz	Cefazolin	2-16	2-16	8-16	–	4-16	8-16	8-16	8-16	4-16	–	Cfz
Cpe	Cefepime	–	–	–	–	–	8-16	8-16	8-16	–	0.25-2	Cpe
Cft	Cefotaxime	–	–	–	–	–	8, 32	8, 32	8, 32	–	0.25-2	Cft
CfxS	Cefoxitin Screen	–	–	–	4	4	–	–	–	4	–	CfxS
Cax	Ceftriaxone	–	4-32	8, 32	8, 32	–	8, 32	8, 32	4-32	4-32	0.25-2	Cax
Crm	Cefuroxime	–	–	–	–	–	–	–	–	–	0.25-2	Crm
Cf	Cephalothin	–	–	–	–	–	8-16	–	–	–	–	Cf
C	Chloramphenicol	8-16	–	8-16	–	–	8-16	–	8-16	8-16	1-16	C
Cp	Ciprofloxacin	1-2	1-2	–	1-2	1-2	1-2	1-2	–	1-2	–	Cp
Cd	Clindamycin	0.25-2	0.25-2	0.5-4	0.5-4	0.5-4	0.5, 2	0.5, 2	0.25-4	0.25-4	0.06-0.5	Cd
Dap	Daptomycin	–	–	0.5-4	0.5-4	0.5-4	–	1, 4	0.25-4	0.25-4	–	Dap
Ert	Ertapenem	–	–	–	–	–	–	2-4	0.5-4	–	–	Ert
E	Erythromycin	0.5-4	0.5-4	0.5-4	0.5-4	0.5-4	0.5, 4	0.5, 4	0.25-4	0.25-4	0.06-0.5	E
Gat	Gatifloxacin	–	2-4	–	–	–	2-4	0.5-4	–	–	0.12-2	Gat
Gm	Gentamicin	1-8	1-8	4-8	4-8	4-8	4-8	4-8	1-8	1-8	–	Gm
GmS	Gentamicin Synergy Screen	500	500	500	500	500	500	500	500	500	–	GmS
Imp	Imipenem	1-8	–	4-8	–	–	4-8	4-8	1-8	4-8	–	Imp
Icd	Inducible Clindamycin Test	–	–	–	4/0.5	4/0.5	–	–	–	4/0.5	–	Icd
Lvx	Levofloxacin	2-4	2-4	2-4	1-4	1-4	2-4	1-4	0.5-4	0.5-4	0.25-4	Lvx
Lzd	Linezolid	0.5-4	0.5-4	1-4	1-4	1-4	2-4	2-4	0.5-4	0.5-4	–	Lzd
Mer	Meropenem	–	–	4-8	–	–	–	–	1-8	2-8	0.06-0.5	Mer
Mxf	Moxifloxacin	–	–	2-4	0.5-4	0.5-4	2-4	0.5-4	2-4	0.5-4	–	Mxf
Fd	Nitrofurantoin	32-64	32-64	32-64	32-64	32-64	32-64	32-64	32-64	32-64	–	Fd
Nxn	Norfloxacin	–	4-8	–	–	–	4-8	–	–	–	–	Nxn
Ofi	Ofloxacin	–	–	–	–	–	2-4	–	–	–	–	Ofi
Ox	Oxacillin	0.25-2	0.25-2	0.25-2	0.25-2	0.25-2	0.25, 1-2	0.25, 1-2	0.25-2	0.25-2	–	Ox
P	Penicillin	0.03, 0.12-0.25, 2, 8	0.03, 0.12-0.25, 2, 8	0.03, 0.12-0.25, 2, 8	0.03, 0.12-0.25, 2, 8	0.03, 0.12-0.25, 2, 8	0.03, 0.12, 2, 8	0.03, 0.12, 2, 8	0.03, 0.12-0.25, 2, 8	0.03-8	0.03-4	P
P/T	Piperacillin/Tazobactam	1-8	–	–	–	–	4-8	4-8	8	–	–	P/T
Rif	Rifampin	1-2	1-2	1-2	1-2	1-2	1-2	1-2	1-2	1-2	–	Rif
StS	Streptomycin Synergy Screen	1000	1000	1000	1000	1000	1000	1000	1000	1000	–	StS
Syn	Synercid	0.25-2	0.25-2	0.5-2	0.5-2	1-2	1-2	1-2	0.25-2	0.25-2	–	Syn
Te	Tetracycline	4-8	4-8	4-8	4-8	4-8	4-8	4-8	1-8	1-8	0.5-4	Te
T/S	Trimethoprim/Sulfamethoxazole	2/38	2/38	0.5/9.5, 2/38	0.5/9.5-2/38	0.5/9.5-2/38	2/38	2/38	0.5/9.5, 2/38	0.5/9.5-2/38	0.25/4.75-2/38	T/S
Va	Vancomycin	2-16	2-16	0.25-16	0.25-16	0.25-16	2-4, 16	2-16	0.25-16	0.25-16	0.12-1	Va
Total Antimicrobics / Panel		22	23	25	24	24	32	29	29	28	18	

Units: µg/mL