

3gAllergy™ ASR Allergen Menu



Allergen Menu	Catalog No.	Allergen Menu	Catalog No.
Animal 20 tests		Foods 20 tests	
E7 Pigeon Droppings	E7L2	F255 Plum	F255L2
E78 Budgerigar Feathers	E78L2	F256 Walnut	F256L2
E85 Chicken Feathers	E85L2	F259 Grape	F259L2
E89 Turkey Feathers	E89L2	F260 Broccoli	F260L2
E91 Parrot Feathers	E91L2	F261 Asparagus	F261L2
E201 Canary Feathers	E201L2	F263 Green Pepper	F263L2
Drugs		F269 Basil	F269L2
C1 Penicilloyl G	C1L2	F270 Ginger	F270L2
C2 Penicilloyl V	C2L2	F279 Chili Pepper	F279L2
C203 Ampicillin	C203L2	F280 Black Pepper	F280L2
Foods		F283 Oregano	F283L2
F21 Sugar Cane	F21L2	F284 Turkey Meat	F284L2
F42 Haddock	F42L2	F287 Red Kidney Bean	F287L2
F50 Chub Mackerel	F50L2	F288 Blueberry	F288L2
F54 Sweet Potato	F54L2	F290 Oyster	F290L2
F65 Perch	F65L2	F291 Cauliflower	F291L2
F82 Cheese, Mold-type	F82L2	F299 Chestnut	F299L2
F86 Parsley	F86L2	F300 Pinto Bean	F300L2
F88 Lamb	F88L2	F303 Halibut	F303L2
F94 Pear	F94L2	F306 Lime	F306L2
F95 Peach	F95L2	F315 Green Bean	F315L2
F102 Cantaloupe	F102L2	F329 Watermelon	F329L2
F105 Chocolate	F105L2	F337 Sole	F337L2
F147 Flounder	F147L2	F338 Scallop	F338L2
F182 Lima Bean	F182L2	F360 Yogurt	F360L2
F202 Cashew	F202L2	F381 Red Snapper	F381L2
F203 Pistachio	F203L2	F403 Brewer's Yeast	F403L2
F204 Trout	F204L2		
F207 Clam	F207L2		
F208 Lemon	F208L2		
F209 Grapefruit	F209L2		
F210 Pineapple	F210L2		
F212 Mushroom	F212L2		
F214 Spinach	F214L2		
F216 Cabbage	F216L2		
F220 Cinnamon	F220L2		
F221 Coffee	F221L2		
F222 Tea	F222L2		
F225 Pumpkin	F225L2		
F234 Vanilla	F234L2		
F236 Whey	F236L2		
F237 Apricot	F237L2		
F242 Cherry	F242L2		
F244 Cucumber	F244L2		
F245 Egg	F245L2		
F253 Pine Nut	F253L2		

Listing of Analyte-Specific Reagents[†] (ASR)
available in the United States

Answers for life.

SIEMENS

3gAllergy™ ASR allergen menu

Allergen Menu		Catalog No.	Allergen Menu		Catalog No.
Mites		20 tests	Weeds		20 tests
D201	Blomia tropicalis	D201L2	W36	Rabbit Bush	W36L2
Molds			W37	Saltbush	W37L2
M12	Aureobasidium pullulans	M12L2	W82	Careless Weed	W82L2
M202	Cephalosporium ASRemonium	M202L2	Molecular		
M207	Aspergillus niger	M207L2	A174	nCan f 1 Canis familiaris	A174L2
M305	Penicillium brevicompactum	M305L2	A295	nDer f 1 Dermatophagoides farinae	A295L2
Occupational			A302	nDer f 2 Dermatophagoides farinae	A302L2
K84	Sunflower Seed	K84L2	A310	nDer p 1 Dermatophagoides pteronyssinus	A310L2
Other Analytes			A316	nDer p 2 Dermatophagoides pteronyssinus	A316L2
O201	Tobacco	O201L2	A345	nFel d 1 Felis domesticus	A345L2
Trees			A3050	nAsp r 1 Aspergillus restrictus	A3050L2
T43	Loblolly Pine	T43L2	F351	nPen m 1 Penaeus monodon	F351L2
T83	Mango Tree	T83L2			
T96	Poplar	T96L2			
T401	Brazilian Peppertree	T401L2			

† Sold in the U.S. as analyte-specific reagents. Analytical and performance characteristics are not established. Intended for use by U.S. laboratories that meet CLIA high complexity requirements.



3gAllergy, IMMULITE, and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc. All other trademarks and brands are the property of their respective owners. Product availability may vary from country to country and is subject to varying regulatory requirements. Please contact your local representative for availability.

Siemens Global Headquarters

Siemens AG
Wittelsbacherplatz 2
80333 Muenchen
Germany

Global Siemens Healthcare Headquarters

Siemens AG
Healthcare Sector
Henkestrasse 127
91052 Erlangen, Germany
Telephone: +49 9131 84 - 0
www.siemens.com/healthcare

Global Division

Siemens Healthcare Diagnostics Inc.
1717 Deerfield Road
Deerfield, IL 60015-0778
USA
www.siemens.com/diagnostics

www.siemens.com/diagnostics