

## Anti-Tg Antikörper

- **Assay Format:** IMMULITE (LKTG), IMMULITE 2000 (L2KTG), IMMULITE 2500 (L5KTG)
- **Messbereich:** bis 3000 IU/ml (WHO 1st IRP 65/93)
- **Analyt. Sensitivität:** 10 IU/ml (IMMULITE) ; 2,2 IU/ml (IMMULITE 2000 ; IMMULITE 2500)

Probanden	System	n	Median (IU/ml)	90%-Bereich (IU/ml)	95. Perc. (IU/ml)	Lit.
Gesunde	IMMULITE IMMULITE 2000 IMMULITE 2500	117		n.n. - 40	40	PILKTG-10 PIL2KTG-15 PIL5KTG-2
Probanden	System	n	Median (IU/ml)	90%-Bereich (IU/ml)	97,5. Perc. (IU/ml)	Lit.
Gesunde < 50a	IMMULITE IMMULITE 2000	117			40	3,4
Gesunde > 50a		117			80	