

## Anti-TPO Antikörper

- **Assay Format:** IMMULITE (LKTO), IMMULITE 2000 (L2KTO), IMMULITE 2500 (L5KTO)
- **Messbereich:** bis 1000 IU/ml (WHO 1st IRP 66/387)
- **Analyt. Sensitivität:** 7 IU/ml (IMMULITE) ; 5 IU/ml (IMMULITE 2000 ; IMMULITE 2500)

Probanden	System	n	Median (IU/ml)	90%-Bereich (IU/ml)	79. Perc. (IU/ml)	Lit.
Gesunde	IMMULITE IMMULITE 2000 IMMULITE 2500	75			35	PILKTO-11 PIL2KTO-15 PIL5KTO-2
Probanden	System	n	Median (IU/ml)	90%-Bereich (IU/ml)	92. Perc. (IU/ml)	Lit.
Gesunde	IMMULITE IMMULITE 2000 IMMULITE 2500	130			35	PILKTO-11 PIL2KTO-15 PILKTO-2
Probanden	System	n	Median (IU/ml)	90%-Bereich (IU/ml)	97,5. Perc. (IU/ml)	Lit.
Gesunde < 50a	IMMULITE IMMULITE 2000	139			35	3,4
Gesunde > 50a		145			100	
Gesunde	IMMULITE IMMULITE 2000 IMMULITE 2500	130			35	PILKTO-11 PIL2KTO-15 PILKTO-2