

Calcitonin

- **Assay Format:** IMMULITE (LKCL), IMMULITE 2000 (L2KCL), IMMULITE 2500 (L5KCL)
- **Messbereich:** 2 - 2000 pg/ml
- **Analyt. Sensitivität:** 2 pg/ml (IMMULITE , IMMULITE 2000 , IMMULITE 2500))
- **Umrechnungsfaktor:** pg/ml x 0,2926 → pmol/l

Probanden	System	n	Median (pg/ml)	abs. Bereich (pg/ml)	95. Perc. (pg/ml)	Lit.
Männer	IMMULITE IMMULITE 2000 IMMULITE 2500	120		n.n. – 18,2	8,4	PILKCL-10 PIL2KCL-11 PIL5KCL-4
Frauen		90		n.n. – 11,5	5,0	