

Gastrin

- **Assay Format:** IMMULITE (LKGA), IMMULITE 2000 (L2KGA), IMMULITE 2500 (L5KGA)
- **Messbereich:** bis 1000 pg/ml (NIBSC 66/138)
- **Analyt. Sensitivität:** 7,5 pg/ml (IMMULITE), 5 pg/ml (IMMULITE 2000 ; IMMULITE 2500)
- **Umrechnungsfaktor:** pg/ml x 0,47664 → pmol/l
pg/ml x 1 → mU/l (NIBSC 66/138)

Probanden	System	n	Median (pg/ml)	95% - Bereich (pg/ml)	97,5. Perc. (pg/ml)	Lit.
Gesunde, nüchtern	IMMULITE	143	32	13 - 115	115	PILKGA-5
Gesunde, nüchtern	IMMULITE 2000	143	32	13 - 115	115	PIL2KGA-9
Gesunde, nüchtern	IMMULITE 2500	143	32	13 - 115	115	PIL5KGA-2