

Myoglobin

- **Assay Format:** IMMULITE (LKMY); IMMULITE 2000 (L2KMY); IMMULITE 2500 (L5KMY); IMMULITE turbo (LSKMY)
- **Messbereich:** bis 1000 ng/ml (IMMULITE , IMMULITE 2000) ; bis 800 ng/ml (IMMULITE 2500, IMMULITE turbo)
- **Analyt. Sensitivität:** 0,5 ng/ml (IMMULITE , IMMULITE 2000); 2 ng/ml (IMMULITE 2500); 2,6 ng/ml (IMMULITE turbo)

Probanden	System	n	Median (ng/ml)	95% - Bereich (ng/ml)	97,5. Perc. (ng/ml)	Lit.
Gesunde	IMMULITE IMMULITE 2000 IMMULITE 2500 IMMULITE turbo	258	25		70	PILKMY-7 PIL2KMY-9 PIL5KMY-4 PILSKMY-6