

Nikotin – Metabolite (Cotinin)

- **Assay Format:** IMMULITE (LKNM), IMMULITE 2000 (L2KNM), IMMULITE 2500 (L5KNM)
- **Messbereich:** bis 500 ng/ml
- **Analyt. Sensitivität:** 2,0 ng/ml (IMMULITE) ; 5,0 ng/ml (IMMULITE 2000, IMMULITE 2500)

Probanden	System	n	Median (ng/ml)	abs. Bereich (ng/ml)	Cut-off (ng/ml)	Lit.
Serum Nichtraucher vs. Raucher	IMMULITE IMMULITE 2000 IMMULITE 2500				25	PILKNM-9 PIL2KNM-5 PIL5KNM-1
Urin Nichtraucher vs. Raucher					500	
Urin Nichtraucher		20		< 10 - 20		
Urin passive Raucher		8		< 10 - 49		
Urin Raucher		24		1125 – 20000		