

Osteocalcin

- **Assay Format:** IMMULITE (LKON), IMMULITE 2000 (L2KON), IMMULITE (L5KON)
- **Messbereich:** bis 100 ng/ml
- **Analyt. Sensitivität:** 0,36 ng/ml (IMMULITE); 0,19 (IMMULITE 2000, IMMULITE 2500)

Probanden	System	n	Median (ng/ml)	95% - Bereich (ng/ml)	97,5. Perc. (ng/ml)	Lit.
Gesunde Erwachsene	IMMULITE	186		< 2,0 - 21,0	21,0	PILKON-1
Gesunde Erwachsene	IMMULITE 2000	186		< 2,0 - 22,0	22,0	PIL2KON-1
Gesunde Erwachsene	IMMULITE 2500	186		< 2,0 - 23,0	23,0	PIL5KON-1