

Theophyllin

- **Assay Format:** IMMULITE (LKTN), IMMULITE 2000 (L2KTN), IMMULITE 2500 (L5KTN)
- **Messbereich:** bis 60 µg/ml
- **Analyt. Sensitivität:** 0,3 µg/ml (IMMULITE ; IMMULITE 2000 ; IMMULITE 2500)

Probanden	System	n	Median (µg/ml)	abs. Bereich (µg/ml)	97,5. Perc. (µg/ml)	Lit.
Therapeutischer Bereich	IMMULITE IMMULITE 2000 IMMULITE 2500			10 - 20		PILKTN-5 PIL2KTN-4 PIL5KTN-2 54
Therapeutischer Bereich	IMMULITE IMMULITE 2000 IMMULITE 2500			5 - 10		PILKTN-5 PIL2KTN-4 PIL5KTN-2 55
Toxischer Bereich	IMMULITE IMMULITE 2000 IMMULITE 2500			> 20		PILKTN-5 PIL2KTN-4 PIL5TKN-2 56