

Thyreoglobulin

- **Assay Format:** IMMULITE (LKTY), IMMULITE 2000 (L2KTY), IMMULITE 2500 (L5KTY)
- **Messbereich:** bis 455 pmol/l (CRM 457)
- **Analyt. Sensitivität:** 0,3 pmol/l (IMMULITE ; IMMULITE 2000 ; IMMULITE 2500)

Probanden	System	n	Median (ng/ml)	95% - Bereich (ng/ml)	97,5. Perc. (ng/ml)	Lit.
Gesunde Probanden	IMMULITE	110	10,2	1,7 – 55,6	55,6	PILKTY-13
Gesunde Probanden	IMMULITE 2000 IMMULITE 2500	110	11,0	1,6 – 59,9	59,9	PIL2KTY-12 PIL5KTY-6