

DHEA-SO₄

- **Assay Format:** Coat-A-Count RIA (TKDS)
- **Messbereich:** 5 – 1 000 µg/dl
- **Analyt. Sensitivität:** 1,1 µd/dl
- **Umrechnungsfaktor:** µg/dl x 0,02714 → µmol/l

Probanden	System	n	Median (µg/dl)	95% - Bereich (µg/dl)	Max. Wert (µg/dl)	Lit.
Frauen	Gamma-Counter	132	170	35 - 430		PITKDS-4
Männer		70	280	80 -560		

Probanden	System	n	Median (µg/dl)	95% - Bereich (µg/dl)	Max. Wert (µg/dl)	Lit.
Schwangere 1. Trimester	Gamma-Counter	74	230			PITKDS-4
Schwangere 2. Trimester		74	105			
Schwangere 1d postpartum		74	65			

Probanden	System	n	5.Perc. (µg/dl)	Median (µg/dl)	95. Perc. (µg/dl)	Lit.
Frauen, 10-19 a	Gamma-Counter	2		140		PITKDS-4
Frauen, 20-29 a		23	65	185	380	
Frauen, 30-39 a		29	45	150	270	
Frauen, 40-49 a		29	32	120	240	
Frauen, 50-59 a		18	26	85	200	
Frauen, 60-69 a		21	13	50	130	
Frauen, 70-79 a		8	17	40	90	
Frauen, 80-89 a		6		26		
Frauen, postmenopausal		60	10	55	190	

Männer, 10-19 a	Gamma-Counter	6		215		PITKDS-4
Männer, 20-29 a		17	280	420	640	
Männer, 30-39 a		21	120	300	520	
Männer, 40-49 a		23	95	250	530	
Männer, 50-59 a		29	70	160	310	
Männer, 60-69 a		37	42	130	290	
Männer, 70-79 a		18	28	80	175	
Männer, 80-89 a		4		36		