



The new dimension in mobile X-ray imaging

MOBILETT XP
MOBILETT XP Hybrid
MOBILETT XP Eco

Answers for life.

SIEMENS

MOBILETT XP

Family of imaging solutions – exceeding your expectations

The name MOBILETT has become synonymous with excellence in mobile X-ray imaging. MOBILETT XP, the advanced platform of mobile X-ray systems from Siemens, exceeds your expectations even further. Coupling remarkable imaging power and quality with easy mobility and increased operator comfort.

The MOBILETT XP family consists of three systems:

MOBILETT XP*, a powerful mobile X-ray system that can be used for multiple applications. It offers easy handling and outstanding X-ray capabilities.

MOBILETT XP Hybrid, a versatile mobile X-ray system that includes conventional outlet, battery, and motor-assisted operation for easy transportation.

MOBILETT XP Eco*, a mobile X-ray imaging system that is ideal for facilities with lower imaging power requirements.

Every member of the MOBILETT XP family is available in a giraffe design to help you create a more relaxing patient environment.

MOBILETT XP – designed to fit in any clinical setting

MOBILETT XP is a lightweight and compact mobile X-ray system with industry-leading arm range. It fits easily into small hospital areas, making it ideal for almost all applications in the ICU, neonatal and pediatric departments, or in the ward.

Thanks to its unmatched power and optimal clinical workflow capabilities, MOBILETT XP provides maximum utilization potential. MOBILETT XP even features optimal range and freedom of positioning – in nearly any clinical setting.



* MOBILETT XP and MOBILETT XP Eco are not commercially available in the United States (U.S.A.)



MOBILETT XP

Featuring a detail-oriented design

MOBILETT XP was designed to meet the challenges facing today's healthcare providers. Developed with high imaging power for heavy duty use in busy hospital environments, MOBILETT XP is ideally suited for the most demanding mobile imaging tasks.

Additionally, its lightweight design and compact size make it easy to place and easy to adjust. Setup is also easy because the X-ray tube is mounted on a double-articulated and counterbalanced arm.

MOBILETT XP features an integrated cable design – eliminating loose cables that can get tangled or caught on objects during transport. The integrated cable design also enables easy arm positioning and makes the system easy to clean.

Get brilliant image quality – quickly

The X-ray examination is easy to complete with the MOBILETT XP. Only a minimum number of settings are required in order to start imaging. MOBILETT XP provides excellent image quality that is comparable to most stationary X-ray systems.

The self-calibrating high imaging output, up to 30 kW and 360 mAs (for 230 V line operation), enables short exposure times down to 1 ms – virtually eliminating motion blurring.

Although MOBILETT XP supports a wide range of applications, the remarkably sharp images, made possible by the short exposure times, enhance its utility in chest imaging and neonatal units.

These qualities make MOBILETT XP the optimal choice for semi-sterile environments such as ICU, CCU, neonatal and pediatric departments, or the ward.



User comfort has never been better

The lightweight design of MOBILETT XP makes it easy for the operator to move the system. A convenient handbrake on the chassis ensures that the system stops safely. Since MOBILETT XP is the lightest system in its class, it offers outstanding maneuverability.

The platform's short wheelbase with polyurethane tires helps to overcome rolling resistance, ensuring that the system glides easily on most surfaces. Offering industry-leading arm range – with a double-articulated, counterbalanced swivel arm system – MOBILETT XP can easily be positioned for imaging in virtually all conceivable projections with the patient recumbent, sitting, or any position in between. Since the unit's head can be freely rotated, all types of projections are easy to adjust – from either side of the bed.

The first push of the hand switch puts the MOBILETT XP in prep mode. Once the unit is ready, you have up to 15 seconds to take the image. Or you can use a remote control to operate the system from up to 30 feet away.



MOBILETT XP Hybrid

High operator convenience and increased power

MOBILETT XP Hybrid combines a motor drive with dual source power for exposures providing high comfort in mobile imaging.

The motor-assisted operation makes the system easy to transport – even over steep inclines or thick carpets.

MOBILETT XP Hybrid has two power sources: longlife rechargeable batteries and a conventional power outlet. This provides for maximum use even when the batteries are not fully charged or discharged. MOBILETT XP Hybrid's powerful batteries manage the X-ray load of a challenging working day.

When operated by battery power, MOBILETT XP Hybrid features up to 10 times more imaging power (30 kW and 360 mAs) than the previous system. It easily handles the most demanding clinical situations, including abdominal and chest imaging, even for obese patients.



MOBILETT XP Eco

The lower power, lower investment mobile X-ray solution

MOBILETT XP Eco provides all the features and advantages of MOBILETT XP, but with lower imaging power. Featuring 20 kW/125 mAs imaging power output, this system is designed to meet low power imaging needs.

Whatever your imaging needs, the MOBILETT XP product family makes X-ray examinations simple and fast for both patients and X-ray staff – without compromising image quality.



MOBILETT XP and MOBILETT XP Eco are not commercially available in the United States (U.S.A.).

The information in this document contains general descriptions of the technical options available and may not always apply in individual cases.

The required features should therefore be specified in each individual case at completion of contract. Siemens reserves the right to modify the design and specifications contained herein without prior notice. Please contact your local Siemens sales representative for the most current information.

Original images always lose a certain amount of detail when reproduced.

In the interest of complying with legal requirements concerning the environmental compatibility of our products (protection of natural resources, waste conservation), we recycle certain components. Using the same extensive quality assurance measures as for new components, we guarantee the quality of these recycled components.

Please find fitting accessories:
www.siemens.com/medical-accessories

Local Contact Information

In USA

Siemens Medical Solutions USA, Inc.
51 Valley Stream Parkway
Malvern, PA 19355-1406 USA
Phone: +1 888 826 9702

In Japan

Siemens-Asahi
Medical Technologies Ltd.
Takanawa Park Tower
3-20-14, Higashi-gotanda
Shinagawa-ku
Tokyo 141-8644
Phone: +81 3 5423 8510

In Asia

Siemens Pte Ltd
The Siemens Center
60 MacPherson Road
Singapore 348615
Phone: +65 6490 8182

In Germany

Siemens AG
Healthcare Sector
Karlheinz-Kaske-Str. 2
91052 Erlangen
Phone: +49 9131 84-0

Global Business Unit

Siemens AG
Medical Solutions
Special Systems
Henkestr. 127
DE-91052 Erlangen
Germany
Phone: +49 9131 84-0

Global Siemens Headquarters

Siemens AG
Wittelsbacherplatz 2
80333 Muenchen
Germany

Global Siemens Healthcare Headquarters

Siemens AG
Healthcare Sector
Henkestr. 127
91052 Erlangen
Germany
Phone: +49 9131 84-0
www.siemens.com/healthcare

Legal Manufacturer

Siemens AG
Wittelsbacherplatz 2
DE-80333 Muenchen
Germany

www.siemens.com/healthcare