



Accessories for Urology

www.usa.siemens.com/medical

SIEMENS
medical

Table Accessories



Cysto Lift Knee Crutch

Cysto Lift Knee Crutch helps neutralize leg weight, allowing the surgeon to move the leg to the desired position intra-operatively. It can accommodate patients that are up to 500 lbs in weight. Socket and pad set are included with purchase.

Order No. **AMFCLKSMNS**



Leg Holders with "Piston Lift"

Leg Holders with "Piston lift" help neutralize leg weight, allowing the surgeon to effortlessly move the leg to the desired lithotomy and abduction positions. The Leg Holders can accommodate patients that are up to 500 lbs in weight. Socket and pad set included with purchase.

Order No. **AMFLHSMNS**

Blade Clamp - Urooskop

Basic blade clamp that is compatible with knee crutches and leg holders when used in conjunction with Siemens Urooskop Access.

Order No. **AMFRC2XUKA3**



Patient Restraint Strap with Hooks

The patient restraint strap attaches to the table rail quickly with stainless steel hooks. It adjusts easily with the use of airplane style buckles. The strap is made of conductive reinforced material for durability and ease of cleaning. Adjusts from 18" to 45". The mid panel is 5" wide. Fits all tables.

Order No. **AMF-PRS**

Restraint Strap Hooks

Attaches to the table side rail quickly and easily. Allows for attachment of Patient Security Strap.

Order No. **AMFPRSH**



Armboard with trigger adjustment

With the trigger design, simply pull the radiolucent release mechanism for full articulation and release it to lock. A spring lever accessible from both sides securely locks the armboard to the rail and eliminates the uncertainty of gravity locks.

Order No. **AMFABSLTE**

Order No. **AMOA1004X10RA** (1" armboard pad)

Ergonomic Accessories



Anti-fatigue Floor Mats by Interstate

Industrial-grade anti-fatigue floor mat provides comfort and durability. As a high-quality product designed to fight fatigue, it provides support for tired, aching feet, legs and backs. Beveled edges for safety. Available in gray or blue (shown in blue).

Order No. **NT60010835** (Gray)

Order No. **NT60010635** (Blue)

Radiation Protection

Stationary Shield

Transparent acrylic protective stationary ceiling mount shield designed to provide maximum scatter protection for the physician.

MAVIG PORTEGRA2 40" x 50" Acrylic Stationary Shield, Long Column includes:

- Mounting kit for installation between two Unistrut® rails, 16" x 28"
- Dual fixture PORTEGRA ceiling column, length 33" for ceilings over 9.5 ft high
- PORTEGRA2 extension/spring arm combination, length 30"/35"
- Center mounted connecting element and radiation protection window 16" x 20", 0.5 mm Pb equivalent

Order No. **M6PT74**



MAVIG PORTEGRA2 40" x 50" Acrylic Stationary Shield, Short Column includes:

- Mounting kit for installation between two Unistrut® rails, 16" x 28"
- Dual fixture PORTEGRA ceiling column, length 18" for ceilings under 9.5 ft high
- PORTEGRA2 extension/spring arm combination, length 30"/35"
- Center mounted connecting element and radiation protection window 16" x 20", 0.5 mm Pb equivalent

Order No. **M6PT74SC**

Consumables

Urology Drain Bag

The urology drain bag was designed specifically for the Siemens Uroskop Access. Made of durable vinyl, this drain bag utilizes an under-buttocks flap to direct fluids into the bag. Case of 20.

Order No. **CF507505**



Urology Drain Collection Bag

Designed to collect waste fluid when a floor drain or suction is not available. Internal baffle system enables the container to fill evenly as powder converts liquid to gel. Built in handles allow the unit to be easily carried to disposal. 5-gallon capacity.

Order No. **CF505406**



Footswitch Covers for UROSKOP Access

Wide Footswitch cover, 24" x 20" fits with latex-free elastic cord and cinch lock, bulk-packaged, non-sterile. Case of 100.

Order No. **CF507506**



Documentation Systems



CODONICS Horizon GS Grayscale Printer

Horizon GS (Grayscale only, no color, large and small format paper and film media) combines the ability of a dry film imager and a grayscale paper imager. This desktop imager supports 14" x 17", 11" x 14" and 8" x 10" film, as well as A and A4 grayscale paper for direct 'room light' viewing. Switching between film and paper is automatic, requiring no operator intervention.

Order No. COHRGSSIEM32

CODONICS Horizon SF Grayscale/Color Printer

Horizon SF (Small format paper and film media, Color and Grayscale) is three imagers in one – a dry film imager, a color imager, and a grayscale paper imager. This desktop imager prints four different media types in three different sizes. Switching between media is automatic, requiring no operator intervention. Horizon supports 8" x 10" film, as well as A and A4 color film, color paper and grayscale paper for direct 'room light' viewing.

Order No. COHRFSIEM34



Sony Black & White Graphic Printer

Black and white video graphics printer that supports both analog and digital applications. Offers resolution of 325 dpi and print speed of 8 seconds. The UP-970AD supports paper only output. The UP-990AD offers thermal paper and blue film output. Includes one year warranty through Sony.

Order No. S2UP970AD (UP970-AD B&W graphic printer)

Order No. S2UP990AD (UP990-AD B&W graphic printer)

Media for Sony's Video graphics printers:

Blue Thermal Transparency Film for the Sony UP980/990

Order No. S2UPT210BL

High Density paper for Sony UP960/970/980/990

Order No. S2UPP210HD

Paper for Sony UP960/970/980/990

Order No. S2UPP210SE

Technical Equipment



PERKINS ELECTRONICS Uroskop Pak

The Uroskop Pak provides real time down scan conversion of the high resolution 'Live' video signal for interfacing to standard line rate devices such as VCR's and Video Printers. Once installed, the scan conversion (video reformatting) of the 'Live' video signal is automatic and no user intervention is required other than to operate the VCR or Video Printer.

Order No. P10SMS01550000

Order direct: 1-888-222-9944 x7

www.usa.siemens.com/medical-accessorysolutions

Endoscopy Equipment

Invisio MegaPixel Autoclavable Direct Coupler Swivel System with DVI

The Invisio™ MegaPixel Autoclavable Cameras feature an all-digital CMOS imaging sensor with 1.3 million pixels for superior resolution and color fidelity. They are light weight, ergonomically designed and available in both right angle and direct coupler configurations.

The hermetically sealed titanium housing of the MegaPixel Autoclavable cameras have been engineered to survive the most damaging handling and sterilization modalities including the rigorous French Autoclave Cycle.



Invisio MegaPixel Autoclavable Direct Coupler Swivel System with DVI

Includes:

- Invisio MegaPixel Autoclavable Direct Coupler Camera Head and Invisio Digital Controller with DVI.
- 1,300,000 pixel resolution.
- NTSC/PAL/VGA/DVI/HD video outputs, remote accessory ports (2), and the following video outputs: BNC (2), Y/C (2), RGB (1), VGA (1), DVI (1) and HD (1) outputs. 110-240VAC; 50/60Hz.
- 2 year warranty through Gyrus ACMI.

Order No. **GYIMP1360**

Invisio MegaPixel Autoclavable Right Angle Swivel System with DVI

All digital 1.3 million pixel CMOS imaging sensor delivers advanced image clarity. Programmable buttons, lightweight, ergonomic design and digital zoom without loss of resolution put physicians in control. Nurses appreciate its rugged design that survives the most damaging handling and sterilization modalities.



Invisio MegaPixel Autoclavable Right Angle Swivel System with DVI

Includes:

- Invisio MegaPixel Autoclavable Right Angle Camera Head and Invisio Digital Controller with DVI.
- 1,300,000 pixel resolution.
- NTSC/PAL/VGA/DVI/HD video outputs, remote accessory ports (2), and the following video outputs: BNC (2), Y/C (2), RGB (1), VGA (1), DVI (1) and HD (1) outputs. 110-240VAC; 50/60Hz.
- 2 year warranty through Gyrus ACMI.

Order No. **GYIMP1365**

Invisio MegaPixel Direct Coupler System with DVI

Invisio MegaPixel Direct Coupler System with DVI Includes:

- Invisio MegaPixel Direct Coupler Camera Head and Invisio Digital Controller with DVI.
- 1,300,000 pixel resolution.
- NTSC/PAL/VGA/DVI/HD video outputs, remote accessory ports (2), and the following video outputs: BNC (2), Y/C (2), RGB (1), VGA (1), DVI (1) and HD (1) outputs. 110-240VAC; 50/60Hz.
- 2 year warranty through Gyrus ACMI.

Order No. **GYIMP1370**



Endoscopy Equipment



Invisio MegaPixel Right Angle Swivel System with DVI

Invisio MegaPixel Right Angle Swivel System with DVI Includes:

- Invisio MegaPixel Right Angle Camera Head with Swivel and Invisio Digital Controller with DVI.
- 1,300,000 pixel resolution.
- NTSC/PAL/VGA/DVI/HD video outputs, remote accessory ports (2), and the following video outputs: BNC (2), Y/C (2), RGB (1), VGA (1), DVI (1) and HD (1) outputs. 110-240VAC; 50/60Hz.
- 2 year warranty through Gyrus ACMI.

Order No. GYIMP1375



Invisio MegaPixel Autoclavable Direct Coupler Camera Head

Invisio MegaPixel Autoclavable Direct Coupler Camera Head

Order No. GYIMP1310



Invisio MegaPixel Autoclavable Right Angle Camera Head

Invisio MegaPixel Autoclavable Right Angle Camera Head

Order No. GYIMP1320



Invisio MegaPixel Direct Coupler Camera Head

Invisio MegaPixel Direct Coupler Camera Head

Order No. GYIMP1330



Invisio MegaPixel Right Angle Camera Head with Swivel

Invisio MegaPixel Right Angle Camera Head with Swivel

Order No. GYIMP1340

Other Accessories

Cable tubing 3 1/2" RD w/Velcro

3 1/2" diameter cable tubing with Velcro closure. White. 15 foot long. Made of PVL which is a tough, lightweight flexible jacket of vinyl-coated polyester. Flame retardant PVC is laminated to both sides of a Polyester fabric to make this rugged jacket extremely flexible and lightweight. This reinforced construction provides good wear resistance combined with high tear strength. It's ideal for discrete wires, wire harnesses, hoses, and other applications where its flexibility, strength and abrasion protection are needed. The jacket conforms to MIL-C-43006E, Type II, Class 1.

Order No. AEZT9713004312W



Uroskop Table Pad

Compression Formed Urology Table pad designed to fit the exact specifications of the Siemens Uroskop Table with integral drain flap.

Order No. CF523601



On account of certain regional limitations of sales rights and service availability, we cannot guarantee that all products included in this brochure are available through the Siemens sales organization worldwide. Availability and packaging may vary by country and is subject to change without prior notice. Some/All of the features and products described herein may not be available in the United States.

The information in this document contains general technical descriptions of specifications and options as well as standard and optional features which do not always have to be present in individual cases.

Siemens reserves the right to modify the design, packaging, specifications and options described herein without prior notice. Please contact your local Siemens sales representative for the most current information.

Note: Any technical data contained in this document may vary within defined tolerances. Original images always lose a certain amount of detail when reproduced.

© 2007 Siemens Medical Solutions USA, Inc.
Order No. A91111-7560-C1-4A00
Printed in USA 05-2007
All rights reserved

Contact Address

Siemens Medical Solutions
Accessory Solutions
51 Valley Stream Parkway
Malvern, PA 19355-1406 USA

Headquarters

Siemens Medical Solutions USA
51 Valley Stream Parkway
Malvern, PA 19355-1406
USA
Telephone: +1-888-826-9702