

# autoSCAN<sup>®</sup>-4 Technical Specifications and Installation Requirements



## Physical

Dimensions	10" H x 19" W x 23" D
Weight	40 lbs.
Power cord length	6'5"
Cable to computer length	8'5"
Digital interface	RS-232C (9600 baud)
AC power plug type	5-15P

## Power

Line voltage	105/115/230 VAC $\pm$ 10 %
Line frequency	60/50 Hz $\pm$ 10 %
Line current	2.00A max. (115V), 1.25A max. (230V)
Heat generation	630 BTU/HR
	Optional Uninterruptible Power Supply (UPS) available

## Optical System

General	Abridged filter photometer with six interference filters (wavelengths in nanometers: 440, 470, 505, 560, 590, 620), 96-channel fiber optics harness
Light source	Tungsten-halogen lamp, 3500 hours
Spectral bandwidth	10 nm

## Analyzer

System panel capacity	1 panel/reading
Read time	Less than 5 seconds

## Safety Requirements

Ground impedance	0.1 ohms max.
Dielectric withstand voltage	No dielectric breakdown (@ 1000 VAC 60 Hz for 1 minute)
Power cord	3-conductor, 16 AWG industrial grade SJT
Overcurrent interrupter	1.60A (115V), .80A (220V)
Leakage current	Less than 500 $\mu$ A

autoSCAN-4 Microbiology System

Answers for life.

**SIEMENS**

## Safety Compliance

The autoSCAN-4 instrument has been designed and tested to comply with safety standards UL3101-1, CSA C22.2#1010.1 and EN61010-1 under the following environmental conditions:


<b>Temperature</b>	5 °C (41 °F) to 40 °C (104 °F)
<b>Humidity</b>	Max. 80% at 31 °C (88 °F) to 50% at 40 °C (104 °F)
<b>Altitude</b>	Max. 2000 m. (6,561 ft.)
<b>Main supply</b>	115/230 VAC, 50/60 Hz, 230 W max.
<b>Overvoltage category</b>	Category II, connected to a branch circuit
<b>Pollution degree</b>	Degree 2, normal indoor laboratory environment. Air contains only non-conductive pollutants with occasional condensation

## Emission Compliance

The autoSCAN-4 instrument has been designed and tested to comply with standard EN61326.

## Product and Peripheral Equipment Dimensions

Specifications are for autoSCAN-4 instrumentation only and do not include peripheral equipment. Dimensions for peripheral equipment are informational only and may change without notice.



autoSCAN®-4 and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc. All other trademarks and brands are the property of their respective owners. Product availability may vary from country to country and is subject to varying regulatory requirements. Please contact your local representative for availability.

### Siemens Global Headquarters

Siemens AG  
Wittelsbacherplatz 2  
80333 Muenchen  
Germany

### Global Siemens Healthcare Headquarters

Siemens AG  
Healthcare Sector  
Henkestrasse 127  
91052 Erlangen, Germany  
Telephone: +49 9131 84 - 0  
[www.siemens.com/healthcare](http://www.siemens.com/healthcare)

### Global Division

Siemens Healthcare Diagnostics Inc.  
1717 Deerfield Road  
Deerfield, IL 60015-0778  
USA  
[www.siemens.com/diagnostics](http://www.siemens.com/diagnostics)

[www.siemens.com/diagnostics](http://www.siemens.com/diagnostics)