



SIEMENS

Where it All Comes Together for a More Efficient Workflow

Dimension Vista Systems Test Menu: Intelligence at work

www.siemens.com/diagnostics

Speed and quality without compromise.

The Dimension Vista® Intelligent Lab System integrates multiple best-in-class technologies into one compact analyzer for unique integration.

- Revolutionary LOCI® Chemiluminescence Technology
- First Time Nephelometry
- Photometry
- V-LYTE® Integrated Multisensor Technology



The Dimension Vista System provides sample workflow consolidation, with over 120 assays today and more to come.

- Integrates complex assays on a core chemistry platform
- Simultaneously processes a diverse menu
- Eliminates many single-use workstations
- Intelligently schedules tests for fast STAT results



For Distribution Outside of the United States

Answers for life.

Dimension VISTA Intelligent Lab System Test Menu

General Chemistry

Albumin
Blood Urea Nitrogen
Calcium
Carbon Dioxide
Creatinine
Enzymatic Creatinine^{3,4}
Magnesium
Phosphorus
Total Protein
Uric Acid

Electrolytes

Chloride
Potassium
Sodium

Diabetes

Glucose
Hemoglobin A1C
Microalbumin

Nutritional Assessment

α1-Acid Glycoprotein (Orosomuroid)
Albumin (Nephelometry)
C-Reactive Protein
Prealbumin (Transthyretin)
Retinol Binding Protein
Transferrin

Hepatic

Alanine Aminotransferase
Albumin
Alkaline Phosphatase
Apolipoprotein A1
Aspartate Aminotransferase
α2-Macroglobulin
Direct Bilirubin
Gamma Glutamyltransferase
Haptoglobin
Lactate Dehydrogenase³
Total Bilirubin
Total Protein

Bone

Alkaline Phosphatase
Calcium Phosphorus
Intact PTH¹
Vitamin D Total¹

Tumor Markers/ Oncology

LOCI AFP
LOCI CA 15-3
LOCI CA 19-9
LOCI CA 125II
LOCI CEA
LOCI Free PSA
LOCI Total PSA

Cardiovascular- Risk Assessment

Apolipoprotein A1
Apolipoprotein B
Cholesterol
High-Density Lipoprotein
Cholesterol
High-Sensitivity CRP (CardioPhase™)
Homocysteine
LOCI BNP
LOCI NT-proBNP
Low-Density Lipoprotein
Cholesterol
Triglycerides

Cardiac – Acute Care

Creatine Kinase³
Creatine Kinase MB Isoenzyme³
High-Sensitivity CRP (CardioPhase)
LOCI BNP
LOCI Cardiac Troponin I
LOCI Mass Creatine Kinase MB Isoenzyme
LOCI Myoglobin
LOCI NT-proBNP

Nephropathies

α1-Microglobulin (U)
α2-Macroglobulin (U)
β2-Microglobulin (U)
Creatinine (S, U)
Cystatin C (S)
Homocysteine
Ig Light Chains, Type Kappa (U)
Ig Light Chains, Type Lambda (U)
Immunoglobulin G (U)
Microalbumin (U)
Specialty Albumin
Total Protein (U)
Transferrin (U)

Anemia/Iron Metabolism

Haptoglobin
Hemopexin
Homocysteine
Iron
LOCI Ferritin
LOCI Folate
LOCI Vitamin B12
Soluble Transferrin Receptor
Total Iron Binding Capacity
Transferrin

Pancreatic

Amylase
Lipase

Thyroids

LOCI FT4
LOCI FT3
LOCI TSH
T-Uptake
T4
T3

Fertility

LOCI β-Human Chorionic Gonadotropin
LOCI Estradiol
LOCI FSH
LOCI LH
LOCI Progesterone¹
LOCI Prolactin
LOCI Testosterone¹

Therapeutic Drug Monitoring

Amikacin²
Caffeine²
Carbamazepine
Digitoxin
Digoxin
Gentamicin
Lidocaine
Lithium
N-acetyl Procainamide
Phenobarbital
Phenytoin
Procainamide
Theophylline
Tobramycin
Valproic Acid
Vancomycin

Immunosuppressive Drugs

Cyclosporine
Cyclosporine Extended (C2)

Specialty

α1-Antitrypsin
Ammonia
Ceruloplasmin
Carbohydrate-Deficient Transferrin¹
Hemopexin
Lactic Acid
LOCI D-Dimer¹
Pseudocholinesterase

Complement Activity

C1 Inhibitor
C3 Complement
C4 Complement

Polyclonal/ Monoclonal Gammopathies/ Immune Systems

β2-Microglobulin
Ig Light Chains, Type Kappa
Ig Light Chains, Type Lambda
Immunoglobulin A
Immunoglobulin E
Immunoglobulin G Subclass 1
Immunoglobulin G Subclass 2
Immunoglobulin G Subclass 3
Immunoglobulin G Subclass 4
Immunoglobulin M

Autoimmune Disease/ Inflammatory Disorders

α1-Acid Glycoprotein (Orosomuroid)
Antistreptolysin O
C-Reactive Protein
C3 Complement
C4 Complement
Rheumatoid Factor

Allergy Testing

Immunoglobulin E

Protein — CSF

Albumin (Nephelometry)
Immunoglobulin G
Lactic Acid
Specialty Albumin
Urinary/Cerebrospinal Fluid Protein

Toxicology

LOCI Digoxin
Serum Acetaminophen
Serum Barbiturates²
Serum Benzodiazepines²
Serum Salicylate
Serum Tricyclic Antidepressants²
Serum/Urine Ethyl Alcohol

Drugs of Abuse

Urine Amphetamine
Urine Barbiturates
Urine Benzodiazepines
Urine Cocaine
Urine Ecstasy
Urine Methadone
Urine Methaqualone²
Urine Opiate
Urine Phencyclidine
Urine Propoxyphene²
Urine Cannabinoids

Metabolic

Homocysteine
Cortisol¹

- Under development. Not available for sale.
- Syva® Emit® applications.
- IFCC approved.
- Not available for sale on the Dimension Vista® 500 and 1000T Systems.

Siemens Healthcare Diagnostics, a global leader in clinical diagnostics, provides healthcare professionals in hospital, reference, and physician office laboratories and point-of-care settings with the vital information required to accurately diagnose, treat, and monitor patients. Our innovative portfolio of performance-driven solutions and personalized customer care combine to streamline workflow, enhance operational efficiency, and support improved patient outcomes.

CardioPhase, Dimension Vista, EMIT, LOCI, V-LYTE, Syva, and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc. All other trademarks and brands are the property of their respective owners.

Product availability may vary from country to country and is subject to varying regulatory requirements. Please contact your local representative for availability.

Global Siemens Headquarters

Siemens AG
Wittelsbacherplatz 2
80333 Muenchen
Germany

Global Siemens Healthcare Headquarters

Siemens AG
Healthcare Sector
Henkestrasse 127
91052 Erlangen
Telephone: +49 9131 84-0
Germany
www.siemens.com/healthcare

Global Division

Siemens Healthcare Diagnostics Inc.
511 Benedict Avenue
Tarrytown, NY 10591-5005
USA
www.siemens.com/diagnostics

Order No. A91DX-110395-XC2-4A00
08-2011 | All rights reserved
© 2011 Siemens Healthcare Diagnostics Inc.