



Eaton Powerware UPS for Artis zee[®] systems

Backup Power Protection and Power Management



UPS supplies full emergency power to all Artis zee functions in case of power failure. Fluoroscopy and image acquisition can be performed.

**Eaton Powerware 9390 – 160kVA
[Siemens Part # EPW9390160UPS]**

Powerware 9390 – 160kVA, Online UPS Electronics Module

160kVA/144kW @ 0.9 pf, 480 volts input/480 volts output, double conversion technology, unit efficiency up to 94%, input current distortion < 4.5%, patented ABM technology, patented HotSync parallel firmware control, scalable architecture, parallel redundancy, and capacity capable.

Integrated Maintenance Bypass

3-circuit breaker (BIB, MBP, MIS), 480V, 35 kAIC, in an 8-inch wide sidecar mounted to the right side of the UPS cabinet.

UPS and Maintenance Bypass Specifications

Cabinet Dimensions: 43.6"W x 31.6"D x 73.7"H
Cabinet Weight: 1,100 lbs.

Single Battery Cabinet System

One (1) IBC-L Integrated Battery Cabinet. 480 VDC - 240 cells, 400A circuit breaker. Backup time @ 0.9pf (160kVA/144kW) of 8 minutes.

Battery Cabinet Dimensions: 42.7"W x 31.6"D x 73.7"H
Battery Cabinet Weight: 3,920 lbs.

Remote Display Panel

Includes HotSync CAN Bridge card for use with remote display panel.

Included Services from Eaton Powerware

Start-up service (5 days/week x 8 hrs).

Plus: One year onsite parts & labor coverage (7 days/week x 24 hrs).

Plus: One year eNotify remote monitoring. Upon request, a ConnectUPS Web/SNMP Card will be installed during start-up at no charge.

Order direct: 1-888-222-9944 x7
www.usa.siemens.com/medical-accessorysolutions



UPS supplies full emergency power to the imaging system, C-arm, and table. Emergency power for fluoroscopy and image acquisition is not included.

Eaton Powerware 9355 – 15kVA
[Siemens Part # EPW935515UPS]

Powerware 9355 – 15kVA with Internal Battery and Input Isolation Transformer

15kVA/13.5kW @ 0.9 pf, Three phase 480 volts input/480 volts output. Double conversion technology, compact footprint for UPS and standard battery, hardwired in/out, low input THD, high efficiency. Built-in maintenance bypass ensures data and system integrity with a complete power management software package for remote monitoring, management, and shutdown over the network with 4 minutes base runtime.

System Dimensions: 12.8"W x 33.7"D x 47.8"H
System Weight: 577 lbs.

Output Transformer Cabinet

Cabinet includes 480V output isolation transformer.

Cabinet Dimensions: 20"W x 34.1"D x 66"H
Cabinet Weight: 535 lbs.

UPS Light Kit

Red/yellow/green light to indicate transition to battery backup.

Included Services from Eaton Powerware

Start-up service (5 days/week x 8 hrs).

Plus: One year onsite parts & labor coverage (7 days/week x 24 hrs).

Plus: eNotify service included (web card and EMP provided at start-up).

Order direct: 1-888-222-9944 x7
www.usa.siemens.com/medical-accessorysolutions



UPS supplies full emergency power to 3 single-plane Artis systems. Fluoroscopy and image acquisition can be performed.

Eaton Powerware 9315 – 300kVA [Siemens Part # EPW9315300UPS]

Powerware 9315 – 300kVA, Online UPS Electronics Module

300kVA/270kW @ 0.9 pf, 480 volts input/480 volts output, building alarm & RMP interfaces, battery management system, 120VAC convenience outlet, modem and eNotify, 7% THD input filter standard.

UPS Cabinet Dimensions: 65.0"W x 31.5"D x 73.5"H
UPS Cabinet Weight: 4,177 lbs.

Battery Cabinet System

Quantity of two (2) Series 1085 battery cabinets each with Powerware Type E39 battery jars. Provides 7 minutes of battery runtime @ 0.9 pf (300kVA/270kW) load.

Battery Cabinet Dimensions (total): 86"W x 31.5"D x 73.5"H
Battery Cabinet Weight (total): 7,850 lbs.

Maintenance Bypass Panel

3-Circuit Breaker (BIB, MBP, MIS), 600A, 480V, 35 kAIC, wall-mounted panel with shunt trip coil and auxiliary contacts.

MBP Cabinet Dimensions: 36"W x 11.5"D x 73"H
MBP Cabinet Weight: 725 lbs.

Remote Monitor Panel

Includes adapter plug for interface connection with the UPS module.

Included Services from Eaton Powerware

Start-up service (5 days/week x 8 hrs).

Plus: One year onsite parts & labor coverage (7 days/week x 24 hrs).

Plus: eNotify service included (web card and EMP provided at start-up).

Order direct: 1-888-222-9944 x7
www.usa.siemens.com/medical-accessorysolutions

On account of certain regional limitations of sales rights and service availability, we cannot guarantee that all products included in this brochure are available through the Siemens sales organization worldwide. Availability and packaging may vary by country and is subject to change without prior notice. Some/All of the features and products described herein may not be available in the United States.

The information in this document contains general technical descriptions of specifications and options as well as standard and optional features which do not always have to be present in individual cases.

Siemens reserves the right to modify the design, packaging, specifications and options described herein without prior notice. Please contact your local Siemens sales representative for the most current information.

Note: Any technical data contained in this document may vary within defined tolerances. Original images always lose a certain amount of detail when reproduced.

Global Business Unit

Siemens AG
Medical Solutions
Special Systems
Henkestrasse 127
DE-91052 Erlangen
Germany
Phone: +49 9131 84-0
www.siemens.com/healthcare

Global Siemens Headquarters

Siemens AG
Wittelsbacherplatz 2
80333 Muenchen
Germany

Global Siemens Healthcare Headquarters

Siemens AG
Healthcare Sector
Henkestrasse 127
91052 Erlangen
Germany
Phone: +49 9131 84-0
www.siemens.com/healthcare

Legal Manufacturer

Eaton Corporation
Eaton Center
1111 Superior Avenue
Cleveland, OH 44114-2586
USA

Distributed by:

Siemens Medical Solutions USA, Inc.
51 Valley Stream Parkway
Malvern, PA 19355-1406
USA

www.siemens.com/healthcare